

## LR10KPlus 10 kN Universal Materials Testing Machine

The LR10KPlus advanced materials testing machine incorporates an extensive range of features making it ideal for performing complex as well as routine testing applications up to 10 kN (2248 lbf). The standard LR10KPlus features a twin column design with a maximum crosshead travel of 950 mm (37.4 in). Extended machine column options (LR10KPlus-E models) for testing high elongation materials are also available.

This bench mounted machine is microprocessor controlled and incorporates world proven 32 bit technology for highly accurate load measurement and rapid data acquisition. The LR10KPlus features an integral user interface consisting of a side mounted control console with large, positive action membrane keys, allowing complex tests to be performed at the touch of a button. A back lit 4 line LCD display shows the test and set-up information in a wide choice of user selectable languages and units.

The stand alone system is capable of storing up to 600 test results from a choice of ten programmable

test set-ups. Test parameters are entered using the keypad in a sequential menu driven format.

For additional flexibility, the LR10KPlus can also be connected to a personal computer with optional Lloyd Instruments NEXYGENPlus material test and control software. NEXYGENPlus software provides almost unlimited testing and results processing capability in a familiar Windows® environment.

The high stiffness frame incorporates a crosshead guidance system to prevent side loading of the sample under test. The crosshead is driven by twin lead screws and a high precision motor to achieve a wide range of speeds throughout the full load range.

A series of highly accurate, interchangeable load cells is available for tension, compression and cycling through zero force measurements. Our extensive range of grips and fixtures support virtually any type of test. The system is ideal for use in production, quality control, educational and research environments.

### Features

- Simple to set up, operate and maintain
- High accuracy load measurement
- Constant load holding
- Data sampling rate 8 kHz
- Load rate control
- Saves up to 600 test results
- 10 programmable test set-ups
- Pre-loading of samples and cycling to load or extension limits
- Multi-stage testing with NEXYGENPlus software
- Extension resolution <0.05 microns
- Multi-lingual display options
- Multi-unit display options
- Flash upgradeable
- Extended column options for testing high extension materials
- Wide selection of load cells, grips, jigs, extensometers, temperature chambers and other accessories

### Specifications


Force Capacity:	
<b>LR10K Plus (Standard)</b>	10 kN (2248 lbf)
<b>LR10K Plus-E (Extended)</b>	10 kN (2248 lbf)
Crosshead Speed Range:	0.01 to 508 mm/min (0.0004 to 20 in/min)
Speed Accuracy:	<0.2% at steady state
Maximum Crosshead Travel:	
<b>LR10K Plus</b>	950 mm (37.4 in)
<b>LR10K Plus-E</b>	1435 mm (56.5 in)
Width Between Columns:	404 mm (16 in)
Minimum Load Resolution:	0.0001 N (load cell specific)
Load Cell Accuracy:	<0.5%
Extension Resolution:	<0.05 microns
Data Sampling Rate:	8 kHz
Display:	40 character x 4 line backlit LCD
Extensometer Inputs:	Digital and Analogue
Load Measuring System:	EN ISO 7500:2004 Class 0.5 ASTM E4
Software:	NEXYGENPlus Data Analysis Software (optional)
Supply Voltage:	230Vac ±10%, 50-60 Hz, Fuse T3.15AH250V 115Vac ±10%, 50-60 Hz, Fuse T6.3AH250V
Weight:	
<b>LR10K Plus</b>	99 kg (218 lb)
<b>LR10K Plus-E</b>	103 kg (227 lb)
Operating Temperature:	5° to 35°C (41° to 95°F)



## Accessories

Item	Part No	Item
<b>XLC Series Load Cells:</b>		<b>Extensometers:</b>
5 N (1.12 lbf)	01/2946	We supply contacting and non-contacting extensometers. For further information see our extensometer specification sheets.
10 N (2.25 lbf)	01/2360	
20 N (4.5 lbf)	01/2950	
50 N (11.25 lbf)	01/2361	
100 N (22.5 lbf)	01/2480	
250 N (56.25 lbf)	01/3048	
500 N (112.5 lbf)	01/2362	<b>Temperature Chambers and High Temperature Furnaces:</b>
1000 N (225 lbf)	01/2419	A range of thermal chambers and furnaces are available. For further information see our specification sheets.
2500 N (562.50 lbf)	01/2363	
5000 N (1124 lbf)	01/2364	
10 kN (2248 lbf)	01/2365	
<b>Application Software:</b>		<b>Splinter Shields:</b>
NEXYGENPlus	40/0771	Splinter shields can be supplied to your specific requirements. Contact Lloyd Instruments for further information.
<b>Grips &amp; Fixtures:</b>		<b>LR10KPlus-CC Large Compression Cage Option:</b>
A wide range of grips and fixtures are available. For further information see our grip specification sheets.		The LR10KPlus machine can be ordered mounted above a floor standing compression cage for larger sample testing. Contact Lloyd Instruments to discuss your specification needs.


## Machine Dimensions



	mm	in
A (Standard machine height)	1555	61.2
A (Extended machine height)	2055	80.9
B	404	16.0
C	820	32.3
D	480	18.9
E (Standard machine travel)	950	37.4
E (Extended machine travel)	1435	56.5



Tensile test



Compression test



Flexure test

## Ordering Information

Model	Part No	Capacity	Description
LR10KPlus	01/3052	10 kN (2248 lbf)	LR10KPlus Materials Testing Machine with Console
LR10KPlus-E	01/3078	10 kN (2248 lbf)	LR10KPlus Materials Testing Machine (Extended) with Console



www.ametek.com

### UK / Head Office

Lloyd Instruments Ltd  
Sleyning Way  
Bognor Regis  
West Sussex, PO22 9ST

Tel +44 (0)1243 833 370  
Fax +44 (0)1243 833 401  
E-mail uk-far.general@ametek.co.uk  
Web www.lloyd-instruments.co.uk

### France

AMETEK S.A.S.  
Rond Point de l'Epine des Champs  
Buro Plus - Bât. D  
78990 Elancourt

Tel +33 (0)1 30 68 89 40  
Fax +33 (0)1 30 68 89 49  
E-mail general@lloyd-instruments@ametek.fr  
Web www.lloyd-instruments.fr

### Germany

AMETEK GmbH  
Rudolf-Diesel-Straße 16  
D-40670 Meerbusch

Tel +49 (0)2159 9136-0  
Fax +49 (0)2159 9136-39  
E-mail info@ametek.de  
Web www.ametek.de

### USA

AMETEK Measurement & Calibration  
Technologies Division  
8600 Somerset Drive  
Largo, Florida 33773

Tel +1 (727) 536 7831  
Fax +1 (727) 539 6882  
E-mail chatillon.fl-lar@ametek.com  
Web www.lloyd-instruments.com  
www.chatillon.com

### Singapore

AMETEK Singapore Pte Ltd  
No. 43 Changi South Avenue 2  
#04-01 Singapore  
#05-12 Techpoint 486164, Singapore

Tel +65 6484 2388  
Fax +65 6481 6588  
E-mail aspl@ametek.com.sg  
Web www.lloyd-instruments.com

### China

AMETEK, Inc. - Shanghai Rep. Office  
Rm 912, Metro Tower  
30 Tian Yao Qiao Road  
Shanghai 200030

Tel +86 21 6426 8111  
Fax +86 21 6426 7818 Ext.12  
E-mail lloyd@ametek.com.cn  
Web www.lloyd-instruments.com